# THERMOPLASTIC OR SPECIAL POLYMER EXTRUDED TUBES WITH REINFORCING SHEATH

## **TUBOL® PEP**

HDPE tube with PVC sheath



#### Description

High density polyethylene extruded and calibrated tube, polyvinyl chloride sheath

#### **Applications**

Pressurised transport of compressed air, lubricant

#### **Fields**

Maintenance, control, process, instrumentation

#### **General characteristics**

• Sparkproof sheath • Calibrated internal tube • Good resistance to impacts and abrasion Very good UV resistance Very good chemical resistance

### Technical data

• Standard: Material suitable for food contact under certain conditions

• Temperature of use: -15°C to +50°C

• Tube: PLASTUB® PEHD translucent or black • Sheath: PLASTUB® GR black -Non flame-propagating PVC type C2 as per NF C 32070 • Recommended connection:

quick-fit connector

#### **Options** (contact us)

- Other diameters Other packaging
- Surface marking
- Other tube and/or sheath colours
- Other qualities of interior tubes
- Other qualities of external sheaths

Nominal internal diameter	Nominal outside diameter	External diameter on sheath	Bending radius*	Operating pressure*	Burst pressure*	Nominal linear weight
(mm)	(mm)	(mm)	(mm)	(bar)	(bar)	(g/m)
4	6	8	35	33	100	46
6	8	10	45	23	70	63
8	10	12	72	18	55	77
10	12	14	105	15	45	92

Nominal internal diameter	Standard packaging Roll Drum		
(mm)	(m)	(m)	
4	100	500	
6	100	500	
8	100	500	
10	100	500	

Standard tolerances: refer to pages 115 to 118. \*Values provided for information purposes for an ambient temperature of 23°C.



Zone Industrielle 63600 AMBERT - France Tel. + 33 (0)4 73 82 44 36

e-mail: plastub@omerin.com www.plastub.fr

The information given in this technical data sheet is indicative and subject to change without prior notice. As the conditions of use and the environment in which the product is used cannot be fully covered in our design work, PLASTUB shall not assume liability for any incidents in the event of inappropriate use and/or not carried out according to best practices and applicable standards.

To ensure optimal use of our products, we recommend full tests in real-life situations.

To this end, our sales department is on hand to supply samples and/or to examine the conditions of comprehensive testing in our laboratories.